



A19 Thermostat for Portable Heaters (Chain Mount and Drop Cord Electrical Connection) Catalog Page

LIT-1927055

2020-04-22



Description

The A19 Series Thermostat is a sturdy compact thermostat designed especially for temporary installations.

Refer to the *Type A19BAG Thermostat for Portable Heaters with Thermostat Extension Cord and Beaded Chain Hanger Product Bulletin (LIT-121040)* for important product application information.

Features

- 6-foot extension cord with piggyback style plug
- NEMA 1 enclosure
- chain mount

Applications

- on/off control of portable space heaters
- agriculture

Repair Information

If the A19 Thermostat for Portable Heater fails to operate within its specifications, replace the unit. For a replacement thermostat, contact the nearest Johnson Controls® representative.

Selection Chart

Table 1: Selection Chart

Product Code Number	Switch Action	Range °F (°C)	Differential °F (°C)	Maximum Bulb Temperature °F (°C)
A19BAG-1C	Single-Pole, Single-Throw (SPST) open high No-Heat position	35 to 95 (2 to 35)	3 (1.7) Non-adjustable	140 (60)

A19 Thermostat for Portable Heaters technical specifications

Table 2: Electrical Ratings

Motor Ratings VAC	120
AC Full Load A	15
AC Locked Rotor As	90

Product warranty

This product is covered by a limited warranty, details of which can be found at www.johnsoncontrols.com/buildingswarranty.

Single point of contact

APAC	Europe	NA/SA
JOHNSON CONTROLS C/O CONTROLS PRODUCT MANAGEMENT NO. 32 CHANGJIJANG RD NEW DISTRICT WUXI JIANGSU PROVINCE 214028 CHINA	JOHNSON CONTROLS WESTENDHOF 3 45143 ESSEN GERMANY	JOHNSON CONTROLS 507 E MICHIGAN ST MILWAUKEE WI 53202 USA

Contact information

Contact your local branch office:
www.johnsoncontrols.com/locations

Contact Johnson Controls:
www.johnsoncontrols.com/contact-us